

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-FEMALE RETURN LOSS (dB)	2.92mm-MALE RETURN LOSS (dB)
100	0.14	46.9	46.2
1000	0.42	35.8	38.5
2000	0.59	37.1	40.2
3000	0.73	37.7	40.8
4000	0.85	41.0	54.0
5000	0.95	32.5	36.7
6000	1.04	37.7	43.3
7000	1.12	31.5	33.6
8000	1.20	32.6	34.2
9000	1.28	35.6	36.4
10000	1.35	35.1	32.4
11000	1.42	28.9	26.9
12000	1.50	26.7	24.7
13000	1.56	26.2	23.5
14000	1.62	28.0	24.8
15000	1.68	28.7	26.3
16000	1.74	26.7	26.3
17000	1.80	27.1	26.2
18000	1.85	32.4	31.4
19000	1.91	37.4	39.7
20000	1.97	34.0	38.4
21000	2.03	28.1	31.4
22000	2.08	26.2	30.6
23000	2.13	26.1	30.5
24000	2.18	24.4	30.9
25000	2.23	27.0	29.8
26000	2.27	28.7	34.8
27000	2.31	31.2	42.3
28000	2.36	32.6	32.4
29000	2.41	27.5	28.4
30000	2.46	28.6	28.2
31000	2.50	26.9	28.1
32000	2.54	30.7	29.6
33000	2.58	30.9	34.7
34000	2.63	32.7	35.1
35000	2.67	29.0	28.5
36000	2.73	26.1	26.4
37000	2.77	28.6	26.2
38000	2.81	31.8	25.8
39000	2.86	34.3	24.9
40000	2.92	27.9	22.9