

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.30	1.91	6.84
0.40	1.57	8.76
0.50	1.39	10.25
0.60	1.28	11.40
0.70	1.21	12.33
0.80	1.16	13.05
0.90	1.12	13.62
1.00	1.07	14.05
3.00	0.79	16.14
5.00	0.74	16.30
10.00	0.71	16.37
19.00	0.74	16.50
28.00	0.76	16.70
37.00	0.78	16.93
46.00	0.81	17.17
55.00	0.83	17.42
64.00	0.85	17.66
73.00	0.87	17.90
82.00	0.88	18.12
91.00	0.90	18.33
100.00	0.92	18.53
110.00	0.94	18.74
120.00	0.96	18.95
130.00	0.98	19.12
140.00	0.99	19.27
150.00	1.01	19.40
160.00	1.03	19.48
170.00	1.05	19.50
180.00	1.08	19.48
190.00	1.09	19.39
200.00	1.11	19.25
210.00	1.13	19.03
220.00	1.15	18.75
230.00	1.17	18.40
240.00	1.20	18.02
250.00	1.23	17.58
260.00	1.25	17.12
270.00	1.28	16.62
280.00	1.29	16.12
290.00	1.31	15.60
300.00	1.33	15.08