

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.15	2.55	6.30
0.20	1.95	8.14
0.25	1.62	9.51
0.50	1.17	13.06
0.75	1.06	14.36
1.00	1.01	15.07
2.00	0.85	16.66
4.00	0.69	18.13
6.00	0.63	18.72
8.00	0.60	18.95
10.00	0.60	19.00
19.00	0.59	18.42
28.00	0.61	17.34
37.00	0.62	16.18
46.00	0.65	15.04
55.00	0.68	13.99
64.00	0.70	12.99
73.00	0.73	12.07
82.00	0.75	11.23
91.00	0.78	10.47
100.00	0.82	9.74
110.00	0.86	9.00
120.00	0.90	8.32
130.00	0.95	7.72
140.00	1.01	7.14
150.00	1.07	6.61
160.00	1.14	6.13
170.00	1.21	5.67
180.00	1.29	5.26
190.00	1.37	4.86
200.00	1.45	4.53
205.00	1.49	4.36
210.00	1.53	4.20
215.00	1.57	4.04
220.00	1.62	3.89
225.00	1.67	3.75
230.00	1.73	3.62
235.00	1.79	3.49
240.00	1.86	3.36
245.00	1.93	3.25
250.00	2.00	3.14