

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
1.00	0.25	29.08
3.00	0.19	34.10
5.00	0.17	36.71
7.00	0.15	38.72
9.00	0.15	40.25
10.00	0.15	40.85
20.00	0.15	45.19
30.00	0.15	49.16
40.00	0.16	51.13
50.00	0.17	50.35
60.00	0.17	48.02
70.00	0.18	46.07
80.00	0.19	44.27
90.00	0.19	42.72
100.00	0.20	41.26
150.00	0.22	36.03
200.00	0.26	32.35
250.00	0.29	30.45
300.00	0.32	29.00
350.00	0.35	27.62
400.00	0.38	26.85
450.00	0.42	26.05
500.00	0.44	25.44
550.00	0.49	25.04
600.00	0.52	24.27
650.00	0.56	23.70
700.00	0.60	23.24
750.00	0.64	23.27
800.00	0.69	23.54
850.00	0.73	23.74
860.00	0.73	23.88
870.00	0.74	24.00
880.00	0.75	24.13
890.00	0.75	24.23
1000.00	0.86	24.61
1050.00	0.87	24.92
1100.00	0.92	24.99
1150.00	0.95	25.98
1200.00	0.99	27.03
1250.00	1.02	27.90
1300.00	1.07	27.71