

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
5.00	0.18	35.70
9.00	0.16	39.34
10.00	0.16	40.07
30.00	0.16	48.22
50.00	0.18	48.47
70.00	0.19	44.20
90.00	0.20	41.81
100.00	0.21	40.73
125.00	0.23	38.95
150.00	0.23	36.98
175.00	0.24	35.45
200.00	0.25	34.53
290.00	0.31	31.05
380.00	0.37	28.08
470.00	0.43	26.00
560.00	0.49	25.94
650.00	0.56	26.35
700.00	0.60	26.15
725.00	0.62	26.15
750.00	0.63	26.22
775.00	0.64	26.32
800.00	0.68	26.45
840.00	0.71	26.76
870.00	0.71	27.84
900.00	0.78	28.64
1000.00	0.86	34.31
1100.00	0.95	31.70
1200.00	1.03	25.63
1300.00	1.13	21.44
1400.00	1.27	17.43
1500.00	1.45	14.58
1600.00	1.68	12.66
1700.00	1.94	10.92