

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
30.00	0.40	12.47
50.00	0.20	16.85
70.00	0.16	20.19
90.00	0.15	23.02
100.00	0.15	24.41
200.00	0.33	33.50
300.00	0.39	27.74
400.00	0.44	22.90
500.00	0.51	19.13
510.00	0.52	18.82
520.00	0.53	18.59
525.00	0.54	18.49
530.00	0.54	18.39
531.00	0.54	18.37
533.00	0.55	18.33
535.00	0.55	18.28
537.00	0.55	18.24
540.00	0.55	18.17
541.00	0.55	18.15
543.00	0.56	18.10
545.00	0.56	18.05
547.00	0.56	18.00
550.00	0.56	17.92
551.00	0.56	17.89
553.00	0.56	17.83
555.00	0.57	17.77
560.00	0.57	17.62
570.00	0.58	17.34
580.00	0.58	17.11
590.00	0.59	16.94
600.00	0.60	16.79
700.00	0.69	15.00
800.00	0.81	13.59
900.00	0.95	12.50
1000.00	1.12	11.21
1100.00	1.32	9.92