

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
1.00	0.37	24.69
3.00	0.27	29.24
4.00	0.26	30.24
4.50	0.25	30.60
5.00	0.25	30.88
6.00	0.25	31.29
8.00	0.24	31.77
10.00	0.26	31.99
50.00	0.28	32.47
90.00	0.31	32.66
100.00	0.32	32.60
300.00	0.40	25.58
500.00	0.48	20.78
700.00	0.54	17.83
900.00	0.63	15.53
1000.00	0.68	14.63
1100.00	0.73	13.95
1200.00	0.77	13.36
1300.00	0.82	12.93
1400.00	0.87	12.58
1500.00	0.92	12.31
1600.00	0.96	12.16
1700.00	1.00	12.12
1800.00	1.04	12.08
1900.00	1.08	12.09
2000.00	1.12	12.19
2100.00	1.18	12.24
2200.00	1.23	12.26
2300.00	1.30	12.23
2400.00	1.36	12.11
2500.00	1.42	11.92
2600.00	1.48	11.73
2700.00	1.56	11.46
2800.00	1.64	11.14
2900.00	1.75	10.73
3000.00	1.86	10.38
3100.00	1.96	10.05
3200.00	2.09	9.71
3300.00	2.23	9.44
3400.00	2.37	9.22
3500.00	2.53	9.29