

Typical Performance Data

| FREQUENCY (MHz) | INSERTION LOSS (dB) | RETURN LOSS (dB) |
|--------------------|---------------------------|------------------------|
| 0.30 | 2.17 | 8.33 |
| 0.40 | 1.88 | 9.99 |
| 0.50 | 1.70 | 11.15 |
| 0.60 | 1.59 | 12.02 |
| 0.70 | 1.51 | 12.72 |
| 0.80 | 1.44 | 13.28 |
| 0.90 | 1.39 | 13.76 |
| 1.00 | 1.34 | 14.17 |
| 2.00 | 1.06 | 16.87 |
| 3.00 | 0.93 | 18.42 |
| 4.00 | 0.86 | 19.49 |
| 5.00 | 0.82 | 20.25 |
| 10.00 | 0.76 | 21.73 |
| 20.00 | 0.78 | 22.20 |
| 30.00 | 0.81 | 22.06 |
| 40.00 | 0.84 | 21.84 |
| 50.00 | 0.86 | 21.55 |
| 75.00 | 0.91 | 20.79 |
| 100.00 | 0.95 | 20.02 |
| 200.00 | 1.09 | 17.00 |
| 250.00 | 1.17 | 15.66 |
| 300.00 | 1.26 | 14.43 |
| 350.00 | 1.35 | 13.49 |
| 400.00 | 1.47 | 12.65 |
| 450.00 | 1.57 | 11.82 |
| 500.00 | 1.70 | 11.14 |
| 600.00 | 1.94 | 9.95 |
| 700.00 | 2.20 | 8.99 |
| 800.00 | 2.51 | 8.21 |
| 900.00 | 2.85 | 7.57 |
| 1000.00 | 3.22 | 7.03 |
| 1100.00 | 3.64 | 6.61 |
| 1200.00 | 4.09 | 6.26 |
| 1300.00 | 4.56 | 5.94 |
| 1400.00 | 5.07 | 5.69 |
| 1500.00 | 5.60 | 5.50 |
| 1600.00 | 6.17 | 5.41 |
| 1700.00 | 6.71 | 5.42 |
| 1800.00 | 6.84 | 5.40 |
| 1900.00 | 6.60 | 5.47 |
| 2000.00 | 6.21 | 5.52 |