

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.03	6.26	2.49
0.05	3.62	4.65
0.07	2.38	6.56
0.09	1.74	8.25
0.10	1.54	9.00
0.15	1.03	12.07
0.20	0.87	14.23
0.25	0.79	15.85
0.30	0.74	17.12
0.35	0.70	18.13
0.40	0.67	18.96
0.45	0.65	19.68
0.50	0.63	20.29
0.60	0.60	21.28
0.70	0.58	22.06
0.80	0.56	22.71
1	0.52	23.72
3	0.38	28.17
5	0.34	29.93
7	0.31	30.75
9	0.31	31.10
10	0.30	31.13
30	0.33	28.13
50	0.37	24.78
70	0.40	22.25
100	0.48	19.43
150	0.58	16.20
200	0.69	13.85
250	0.76	12.17
300	0.95	10.83
350	1.15	9.75
400	1.44	8.85
450	1.55	8.12
500	1.71	7.59
550	1.97	7.10
600	2.27	6.74
650	2.50	6.48
700	2.71	6.31
800	3.17	6.24
900	2.94	6.58
1000	2.32	7.42