

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
1.00	2.83	8.25
3.00	1.80	12.65
5.00	1.55	14.48
7.00	1.45	15.45
10.00	1.40	16.13
30.00	1.40	16.81
50.00	1.44	16.64
70.00	1.49	16.36
90.00	1.53	16.00
100.00	1.55	15.79
120.00	1.59	15.38
140.00	1.64	14.94
160.00	1.70	14.49
180.00	1.75	14.04
200.00	1.81	13.60
202.00	1.82	13.55
204.00	1.82	13.51
206.00	1.83	13.47
208.00	1.84	13.43
210.00	1.84	13.39
220.00	1.88	13.17
240.00	1.94	12.77
260.00	2.02	12.37
280.00	2.09	11.99
300.00	2.16	11.64
310.00	2.20	11.48
315.00	2.22	11.40
320.00	2.24	11.32
340.00	2.31	11.01
360.00	2.39	10.71
380.00	2.47	10.43
400.00	2.55	10.16
450.00	2.76	9.60
500.00	2.97	9.08
550.00	3.19	8.67
600.00	3.41	8.29
700.00	3.82	7.68
800.00	4.21	7.23
900.00	4.57	6.88
1000.00	4.88	6.60