

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10.00	0.18	40.94
14.00	0.18	43.11
18.00	0.18	44.75
22.00	0.19	46.17
26.00	0.18	47.68
30.00	0.18	49.09
34.00	0.19	50.52
38.00	0.19	50.67
42.00	0.20	51.21
46.00	0.20	50.38
50.00	0.20	50.16
75.00	0.23	44.92
100.00	0.24	41.65
166.00	0.27	35.36
232.00	0.30	32.22
298.00	0.35	29.79
364.00	0.38	28.09
430.00	0.42	26.51
444.00	0.43	26.29
458.00	0.45	26.11
472.00	0.45	25.85
486.00	0.46	25.69
500.00	0.47	25.52
570.00	0.52	24.68
640.00	0.57	24.07
710.00	0.63	23.75
780.00	0.67	23.68
850.00	0.74	23.77
860.00	0.74	23.82
880.00	0.75	23.93
900.00	0.79	24.02
910.00	0.80	23.98
920.00	0.81	24.03
930.00	0.81	24.04
940.00	0.81	24.03
950.00	0.81	24.13
960.00	0.81	24.41
970.00	0.82	24.60
980.00	0.83	24.72
990.00	0.85	24.97
1000.00	0.87	25.04