

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
1300.00	0.36	9.53
1500.00	0.37	9.44
1700.00	0.55	9.57
1900.00	0.79	10.32
2000.00	0.88	10.97
2100.00	0.90	11.87
2200.00	0.90	12.89
2300.00	0.80	14.33
2400.00	0.69	16.40
2450.00	0.56	17.50
2500.00	0.52	19.09
2510.00	0.49	19.39
2520.00	0.49	19.69
2530.00	0.47	19.96
2540.00	0.46	20.15
2550.00	0.43	20.38
2560.00	0.41	20.58
2570.00	0.42	20.84
2580.00	0.38	21.10
2590.00	0.37	21.40
2600.00	0.36	21.64
2610.00	0.34	21.90
2620.00	0.34	22.10
2630.00	0.33	22.18
2640.00	0.37	22.17
2650.00	0.35	22.08
2660.00	0.35	21.85
2670.00	0.37	21.60
2680.00	0.37	21.29
2686.00	0.36	21.15
2700.00	0.36	20.75
2750.00	0.39	19.36
2800.00	0.48	17.25
2900.00	0.67	14.13
3000.00	0.79	13.35
3100.00	0.86	12.75
3200.00	0.93	12.25
3300.00	1.04	11.66
3500.00	1.05	11.65
3700.00	1.04	11.66