

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.20	1.62	10.90
0.30	1.35	13.46
0.40	1.23	15.13
0.50	1.15	16.31
0.60	1.10	17.17
0.70	1.05	17.90
0.80	1.00	18.47
0.90	0.97	19.05
1.00	0.93	19.57
10.00	0.54	31.19
40.00	0.57	27.04
70.00	0.62	22.90
100.00	0.68	20.08
150.00	0.79	16.82
200.00	0.89	14.55
250.00	1.04	12.83
260.00	1.06	12.54
270.00	1.07	12.25
280.00	1.10	11.98
290.00	1.13	11.71
300.00	1.17	11.45
350.00	1.32	10.32
400.00	1.49	9.38
450.00	1.59	8.58
500.00	1.79	7.88
550.00	1.86	7.29
600.00	2.04	6.76
610.00	2.05	6.65
620.00	2.05	6.56
630.00	2.07	6.46
640.00	2.09	6.37
650.00	2.13	6.29
660.00	2.16	6.16
670.00	2.20	6.07
680.00	2.22	5.99
690.00	2.25	5.91
700.00	2.26	5.84
710.00	2.27	5.76