

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
30.00	1.76	8.27
50.00	1.52	9.60
70.00	1.40	10.47
90.00	1.33	11.11
100.00	1.31	11.39
130.00	1.26	12.17
160.00	1.22	12.99
190.00	1.19	13.92
220.00	1.17	14.98
250.00	1.16	16.26
280.00	1.16	17.78
290.00	1.16	18.31
300.00	1.16	18.83
310.00	1.16	19.32
320.00	1.16	19.77
330.00	1.17	20.15
340.00	1.18	20.43
350.00	1.19	20.58
360.00	1.20	20.56
370.00	1.22	20.34
380.00	1.23	19.94
390.00	1.25	19.38
400.00	1.28	18.72
410.00	1.31	17.99
420.00	1.34	17.26
430.00	1.37	16.52
440.00	1.41	15.81
450.00	1.46	15.12
460.00	1.50	14.45
480.00	1.61	13.19
520.00	1.87	10.97