

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
125.00	1.29	7.13
200.00	0.73	10.66
275.00	0.57	13.23
350.00	0.49	15.15
425.00	0.46	16.75
500.00	0.47	17.83
750.00	0.54	18.18
1000.00	0.59	16.99
1083.33	0.61	16.73
1166.67	0.63	16.53
1250.00	0.66	16.44
1327.78	0.69	16.40
1405.56	0.73	16.43
1483.33	0.78	16.46
1561.11	0.83	16.50
1638.89	0.85	16.58
1716.67	0.91	16.66
1794.44	0.96	16.73
1872.22	0.99	16.66
1950.00	0.99	16.61
2010.00	1.02	16.55
2070.00	1.01	16.44
2130.00	1.03	16.40
2190.00	1.11	16.35
2250.00	1.08	16.39
2327.78	1.15	16.48
2405.56	1.22	16.56
2483.33	1.27	16.69
2561.11	1.28	17.03
2638.89	1.29	17.48
2716.67	1.31	18.02
2794.44	1.36	18.71
2872.22	1.44	19.11
2950.00	1.46	19.36
3125.00	1.57	17.69
3300.00	1.77	15.01
3475.00	1.75	12.55
3650.00	2.19	10.81