

RF Transformer

TC1.5-ED9884A/1

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100.0	0.74	9.32
300.0	0.31	18.41
500.0	0.30	22.94
700.0	0.35	25.94
900.0	0.39	24.70
1000.0	0.42	24.38
1100.0	0.45	23.77
1200.0	0.48	22.64
1300.0	0.50	21.09
1400.0	0.53	20.26
1500.0	0.54	19.52
1550.0	0.56	19.27
1600.0	0.57	18.93
1650.0	0.57	18.77
1700.0	0.60	18.35
1750.0	0.59	17.89
1800.0	0.61	17.39
1850.0	0.62	17.16
1900.0	0.62	17.18
1950.0	0.62	17.05
2000.0	0.64	17.27
2050.0	0.64	17.04
2100.0	0.65	17.07
2150.0	0.67	16.88
2200.0	0.68	16.75
2250.0	0.69	16.54
2300.0	0.70	16.57
2350.0	0.72	16.73
2400.0	0.74	16.97
2450.0	0.75	17.47
2500.0	0.77	17.86
2600.0	0.80	18.19
2700.0	0.84	18.49
2800.0	0.89	19.70
2900.0	0.96	22.25
3000.0	1.07	24.89
3100.0	1.23	24.53
3200.0	1.45	22.96
3300.0	1.80	19.36