

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.03	3.58	5.42
0.05	2.17	7.34
0.07	1.46	8.86
0.10	0.94	10.89
0.15	0.60	13.67
0.20	0.47	15.85
0.25	0.42	17.61
0.30	0.39	19.03
0.50	0.34	22.91
0.70	0.33	25.24
0.90	0.31	26.81
2	0.27	30.36
4	0.23	31.22
6	0.22	30.87
8	0.21	30.33
10	0.21	29.77
30	0.26	24.96
50	0.32	21.68
70	0.37	19.30
90	0.44	17.47
100	0.47	16.70
125	0.57	15.05
150	0.66	13.71
175	0.74	12.60
200	0.87	11.65
225	1.00	10.82
250	1.08	10.10
275	1.19	9.48
300	1.37	8.91
325	1.52	8.41
350	1.60	7.96
375	1.78	7.54
400	2.02	7.16
425	2.15	6.80
450	2.31	6.46
475	2.64	6.14
500	2.92	5.83
525	3.14	5.52
550	3.57	5.21
575	4.16	4.90
600	4.74	4.60