

---

*Typical Performance Data*

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | RETURN<br>LOSS<br>(dB) |
|--------------------|---------------------------|------------------------|
| 200.00             | 1.33                      | 6.74                   |
| 210.00             | 1.26                      | 6.88                   |
| 300.00             | 1.22                      | 8.07                   |
| 550.00             | 0.92                      | 9.54                   |
| 800.00             | 0.88                      | 10.68                  |
| 950.00             | 0.82                      | 13.05                  |
| 1100.00            | 0.70                      | 21.93                  |
| 1300.00            | 1.53                      | 10.04                  |
| 1350.00            | 1.77                      | 7.15                   |
| 1400.00            | 2.77                      | 5.05                   |