

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
25	6.98	0.98
50	4.23	2.88
60	3.58	3.70
80	2.64	5.26
100	2.03	6.64
120	1.60	7.85
140	1.28	8.90
150	1.16	9.37
160	1.05	9.82
170	0.95	10.24
180	0.87	10.63
190	0.80	11.00
200	0.73	11.35
210	0.67	11.67
220	0.62	11.97
230	0.58	12.25
240	0.53	12.53
250	0.50	12.77
260	0.47	12.98
270	0.44	13.17
280	0.41	13.35
290	0.39	13.52
300	0.37	13.66
325	0.33	13.97
350	0.30	14.18
400	0.28	14.31
450	0.31	14.15
460	0.32	14.07
470	0.34	13.99
480	0.35	13.90
490	0.37	13.82
500	0.39	13.72
550	0.51	13.14
600	0.66	12.43
650	0.79	11.67
700	0.83	10.91
750	0.79	10.18
800	2.79	9.49
850	10.75	8.84
900	21.78	8.30
1000	12.18	7.53