

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.30	1.45	12.33
0.60	1.13	15.80
0.90	1.01	17.36
1.00	0.97	17.76
1.50	0.85	19.38
2.00	0.76	20.59
3.00	0.67	22.34
4.00	0.62	23.54
5.00	0.59	24.38
6.00	0.57	25.00
10.00	0.55	26.19
20.00	0.55	26.92
25.00	0.56	27.09
30.00	0.56	27.01
40.00	0.57	26.90
50.00	0.57	27.38
51.00	0.57	27.36
52.00	0.57	27.35
60.00	0.58	27.20
70.00	0.59	27.10
71.00	0.59	27.09
72.00	0.59	27.08
73.00	0.59	27.07
74.00	0.59	27.05
75.00	0.59	27.04
76.00	0.59	27.02
77.00	0.59	27.03
78.00	0.59	27.00
79.00	0.59	27.01
80.00	0.60	26.99
100.00	0.61	26.65
200.00	0.66	24.44
300.00	0.72	21.68
350.00	0.77	20.34
400.00	0.81	19.08
500.00	0.94	16.59
600.00	1.12	14.31
700.00	1.38	12.34
800.00	1.71	10.69
900.00	2.16	9.30
1000.00	2.71	8.29