

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
80.00	1.14	12.18
90.00	1.00	12.55
100.00	0.89	12.89
200.00	0.54	14.66
300.00	0.50	14.82
400.00	0.50	14.58
500.00	0.50	14.25
600.00	0.50	14.08
700.00	0.49	14.18
800.00	0.47	14.53
820.00	0.47	14.63
840.00	0.46	14.73
860.00	0.45	14.87
880.00	0.45	15.09
900.00	0.43	15.40
920.00	0.43	15.74
940.00	0.42	16.05
960.00	0.41	16.33
980.00	0.40	16.62
1000.00	0.39	17.02
1050.00	0.37	18.47
1100.00	0.35	19.68
1150.00	0.34	21.16
1200.00	0.35	22.43
1250.00	0.35	22.48
1300.00	0.36	21.77
1350.00	0.39	19.45
1400.00	0.43	17.40
1500.00	0.58	13.25
1600.00	0.82	10.14
1700.00	1.12	8.02
1800.00	1.52	6.61
1900.00	1.96	5.49
1950.00	2.23	4.96
2000.00	2.49	4.44
2050.00	2.72	4.13
2100.00	2.99	3.74
2150.00	3.17	3.52
2200.00	3.40	3.38
2250.00	3.65	3.07
2300.00	3.84	2.96