

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.50	0.55	16.78
0.70	0.52	18.79
0.90	0.50	20.09
1.00	0.49	20.58
3.00	0.34	25.54
5.00	0.28	28.16
7.00	0.26	29.75
9.00	0.25	30.70
10.00	0.25	30.96
15.00	0.24	30.77
20.00	0.25	29.53
25.00	0.26	28.21
30.00	0.26	26.87
35.00	0.27	25.66
40.00	0.29	24.55
45.00	0.29	23.56
50.00	0.29	22.67
55.00	0.30	21.89
60.00	0.31	21.15
65.00	0.32	20.48
70.00	0.33	19.87
75.00	0.35	19.29
80.00	0.36	18.75
85.00	0.38	18.26
90.00	0.39	17.82
95.00	0.40	17.37
100.00	0.42	16.97
125.00	0.46	15.25
150.00	0.55	13.84
175.00	0.63	12.65
200.00	0.77	11.66
225.00	0.84	10.87
250.00	0.91	10.22
275.00	1.05	9.64
300.00	1.21	9.13
325.00	1.35	8.71
350.00	1.40	8.43