

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.10	1.68	12.05
0.12	1.39	12.64
0.15	1.02	13.82
0.16	0.87	14.39
0.18	0.82	14.93
0.19	0.73	15.45
0.28	0.53	18.02
0.37	0.47	19.84
0.55	0.37	22.17
0.78	0.34	23.81
1.00	0.29	24.84
5.00	0.08	32.19
10.00	0.05	34.89
20.00	0.05	36.22
30.00	0.07	36.67
40.00	0.06	36.60
50.00	0.08	36.38
60.00	0.08	36.44
75.00	0.10	36.56
80.00	0.11	36.46
90.00	0.10	36.47
100.00	0.10	36.54
200.00	0.15	36.00
300.00	0.17	31.22
400.00	0.20	28.66
500.00	0.27	27.25
600.00	0.31	26.27
700.00	0.37	25.70
800.00	0.41	25.74
900.00	0.46	25.70
1000.00	0.53	25.70
1200.00	0.66	25.89
1400.00	0.86	27.28
1600.00	1.17	37.92
1800.00	1.69	27.17
2000.00	2.52	18.38
2100.00	2.77	15.83
2200.00	2.75	13.89
2300.00	2.75	12.35
2400.00	2.89	11.10