

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
350	4.19	3.18
400	3.01	4.52
450	2.18	6.10
500	1.61	7.93
550	1.23	10.03
650	0.82	15.23
700	0.72	18.61
750	0.68	22.60
800	0.66	26.25
810	0.67	26.63
820	0.67	26.80
830	0.67	26.77
840	0.67	26.57
850	0.67	26.23
860	0.67	25.81
870	0.68	25.33
880	0.68	24.83
890	0.68	24.34
900	0.69	23.89
910	0.69	23.46
920	0.70	23.05
930	0.70	22.67
940	0.71	22.31
950	0.71	21.98
960	0.72	21.66
970	0.72	21.35
980	0.73	21.07
990	0.74	20.81
1000	0.74	20.59
1100	0.79	19.39
1150	0.81	19.36
1200	0.83	19.60
1250	0.85	20.12
1300	0.87	20.98
1350	0.89	22.23
1400	0.92	23.91
1450	0.95	25.99
1500	0.99	28.11
1550	1.04	28.29
1600	1.10	26.09
1650	1.19	23.36
1700	1.29	21.02
1750	1.42	19.01
1800	1.60	17.39
1850	1.83	15.95
1900	2.16	14.66
1950	2.64	13.33
2000	3.38	11.88
3000	4.15	5.80
3200	3.63	6.14
3400	4.25	4.83
3800	3.59	18.21
4000	3.50	12.67