

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.5	0.07	27.07	400	4.76
1	0.10	28.42	410	4.22
5	26.48	0.27	420	3.78
20	62.50	0.23	450	2.98
50	82.97	0.18	460	2.81
200	52.90	0.22	480	2.50
210	49.49	0.24	500	2.29
290	24.12	0.49	520	2.07
300	21.04	0.58	540	1.88
350	6.34	2.68	560	1.76
375	2.14	8.78	580	1.67
400	1.06	21.36	600	1.58
450	0.75	29.23	620	1.46
500	0.70	20.03	640	1.38
560	0.72	15.26	660	1.34
600	0.69	14.69	700	1.25
660	0.66	15.61	720	1.18
700	0.58	17.22	740	1.15
760	0.52	21.50	760	1.14
800	0.50	27.10	800	1.07
900	0.53	24.25	850	1.00
950	0.61	19.11	900	0.94
1000	0.66	15.99	950	0.90
2000	2.60	7.89	1000	0.86