

Switch SPDT , 50W

TOSW-425+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB) IN-OUT , "ON"	ISOLATION (dB) IN-OUT , "OFF"	VSWR		
			IN	OUT , "ON" (:1)	OUT , "OFF"
10	1.22	74.41	1.35	1.40	27.25
20	1.06	70.64	1.19	1.22	27.08
50	0.97	61.72	1.11	1.13	27.42
100	0.94	56.09	1.10	1.11	26.82
200	0.90	49.80	1.13	1.12	26.58
408	1.01	45.66	1.21	1.18	26.03
500	1.06	44.93	1.25	1.20	24.98
670	1.10	44.06	1.30	1.24	24.36
857	1.30	43.15	1.35	1.25	22.45
1000	1.39	44.52	1.37	1.24	20.59
1118	1.48	42.72	1.37	1.23	19.44
1250	1.37	42.75	1.36	1.22	19.15
1392	1.51	44.07	1.34	1.20	18.57
1579	1.47	40.41	1.31	1.16	17.15
1778	1.52	37.07	1.30	1.14	16.04
2002	1.66	34.27	1.30	1.16	13.88
2176	1.81	30.64	1.30	1.21	12.25
2363	1.82	26.86	1.28	1.28	9.41
2438	2.08	25.66	1.29	1.30	7.81
2500	2.14	25.03	1.30	1.31	7.10

