

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.03	3.08	7.51
0.04	2.44	8.69
0.05	2.02	9.59
0.06	1.71	10.41
0.07	1.50	11.17
0.08	1.34	11.89
0.09	1.22	12.56
0.10	1.12	13.19
0.20	0.76	17.54
0.30	0.64	20.00
0.50	0.54	22.98
0.70	0.48	24.83
0.90	0.45	26.19
1.00	0.43	26.76
3.00	0.33	32.50
5.00	0.31	34.46
7.00	0.31	35.04
9.00	0.31	34.99
10.00	0.31	34.83
20.00	0.33	32.27
30.00	0.35	29.78
35.00	0.36	28.74
40.00	0.37	27.80
50.00	0.38	26.19
70.00	0.41	23.68
90.00	0.45	21.78
100.00	0.46	20.99
150.00	0.55	17.83
200.00	0.66	15.59
250.00	0.78	13.88
300.00	0.95	12.50
350.00	1.11	11.43
400.00	1.41	10.56
425.00	1.56	10.23
450.00	1.68	9.98
475.00	1.95	9.80
500.00	2.29	9.71
525.00	2.59	9.73
550.00	3.00	9.84
575.00	3.65	10.10
600.00	4.38	10.57