

RF Transformer

TRS2-ED13383/2

Typical Performance Data

FREQUENCY MHz	INSERTION LOSS (dB)	RETURN LOSS (dB)
10.00	0.63	18.73
20.00	0.60	19.25
30.00	0.60	19.33
40.00	0.60	19.35
50.00	0.61	19.31
60.00	0.62	19.28
70.00	0.62	19.23
80.00	0.63	19.19
90.00	0.63	19.15
100.00	0.64	19.10
150.00	0.65	18.87
200.00	0.65	18.57
250.00	0.65	18.29
300.00	0.65	17.95
350.00	0.65	17.60
400.00	0.65	17.32
450.00	0.65	17.00
500.00	0.65	16.72
550.00	0.65	16.45
600.00	0.66	16.16
650.00	0.66	15.89
700.00	0.67	15.62
750.00	0.67	15.35
800.00	0.68	15.11
850.00	0.69	14.82
900.00	0.70	14.59
950.00	0.71	14.31
1000.00	0.73	14.08
1050.00	0.74	13.82
1100.00	0.76	13.56
1200.00	0.80	13.04
1300.00	0.85	12.53
1400.00	0.90	12.03
1500.00	0.97	11.51
1600.00	1.04	10.99
1700.00	1.13	10.45
1800.00	1.23	9.91
1900.00	1.35	9.39
2000.00	1.47	8.88
2100.00	1.61	8.39
2200.00	1.76	7.94