

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.08	3.27	4.10
0.09	2.92	4.72
0.10	2.63	5.33
0.11	2.40	5.91
0.12	2.20	6.46
0.14	1.90	7.50
0.17	1.60	8.86
0.20	1.40	10.02
0.30	1.08	12.84
0.50	0.90	15.84
0.70	0.81	17.41
1.00	0.72	18.96
3.00	0.49	24.13
5.00	0.44	26.18
7.00	0.42	27.06
9.00	0.43	27.46
10.00	0.43	27.58
30.00	0.48	27.22
50.00	0.51	26.62
60.00	0.52	26.40
70.00	0.52	26.18
80.00	0.54	25.96
90.00	0.54	25.70
100.00	0.55	25.40
150.00	0.58	23.55
200.00	0.60	21.72
250.00	0.64	19.63
300.00	0.66	17.53
350.00	0.71	15.82
400.00	0.74	13.99
450.00	0.86	12.31
500.00	1.01	11.04
550.00	1.21	9.72
600.00	1.60	8.57
625.00	1.81	8.08
650.00	2.03	7.57
675.00	2.33	7.07
700.00	2.77	6.62
725.00	3.18	6.22
750.00	3.55	5.87
775.00	4.06	5.48