

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.01	0.05	35.83	36.04
0.05	0.12	37.86	37.75
0.1	0.17	37.43	37.14
0.5	0.40	37.32	39.05
1.0	0.57	33.49	33.32
1.5	0.71	33.33	31.41
2.0	0.83	30.89	29.30
2.5	0.92	29.59	27.69
3.0	1.03	29.77	28.40
3.5	1.11	32.15	30.64
4.0	1.19	30.31	29.19
4.5	1.27	35.67	35.66
5.0	1.35	34.27	35.21
5.5	1.42	34.37	34.53
6.0	1.49	37.72	38.91
6.5	1.56	35.21	35.94
7.0	1.62	33.81	34.23
7.5	1.68	34.82	35.49
8.0	1.75	34.66	33.70
8.5	1.81	32.77	35.97
9.0	1.87	31.86	34.49
9.5	1.93	29.24	31.05
10.0	1.99	28.77	31.64
10.5	2.06	27.52	31.20
11.0	2.10	27.05	30.31
11.5	2.16	26.41	29.33
12.0	2.22	25.74	28.18
12.5	2.28	25.53	28.06
13.0	2.32	26.38	28.51
13.5	2.36	27.39	29.70
14.0	2.42	28.95	30.87
14.5	2.46	31.12	32.76
15.0	2.52	33.58	34.33
15.5	2.57	36.14	36.36
16.0	2.62	36.09	35.50
16.5	2.67	35.73	34.32
17.0	2.72	35.42	32.90
17.5	2.78	35.18	32.05
18.0	2.83	35.75	31.77

