

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.3	0.33	29.34
1.0	0.33	29.07
5.0	0.35	27.58
10.0	0.38	24.97
15.0	0.43	22.60
20.0	0.50	20.67
23.0	0.54	19.73
24.0	0.56	19.45
25.0	0.57	19.19
26.0	0.59	18.94
27.0	0.60	18.71
28.0	0.62	18.49
29.0	0.64	18.28
30.0	0.65	18.08
31.0	0.67	17.90
35.0	0.74	17.29
40.0	0.82	16.78
45.0	0.91	16.52
49.0	0.97	16.51
50.0	0.98	16.52
52.0	1.01	16.60
55.0	1.05	16.77
60.0	1.12	17.18
65.0	1.20	17.62
70.0	1.30	17.77
75.0	1.43	17.16
80.0	1.63	15.43
85.0	1.97	12.69
90.0	2.59	9.48
95.0	3.72	6.49
100.0	5.58	4.20
105.0	8.14	2.76
110.0	11.14	1.96
115.0	14.29	1.54
120.0	17.42	1.31
130.0	23.25	1.10
140.0	28.36	1.01
150.0	32.73	0.94
160.0	36.46	0.90
170.0	39.67	0.86
180.0	42.53	0.82
190.0	45.18	0.78
200.0	47.76	0.75
250.0	69.94	0.60
300.0	56.87	0.50
350.0	53.02	0.42
400.0	51.95	0.35
450.0	51.83	0.30
500.0	52.28	0.27
600.0	54.54	0.22
700.0	58.34	0.20
800.0	68.12	0.18
900.0	60.95	0.18
1000.0	49.86	0.19
1100.0	39.99	0.23
1200.0	24.93	0.57