

Waveguide WR15 UG385/U to 1.85mm-F**WR15-185+***Typical Performance Data (+25°C)*

FREQ.	INSERTION LOSS	1.0mm-FEMALE VSWR
(GHz)	(dB)	(:1)
50.0	-0.11	1.17
50.5	-0.11	1.16
51.0	-0.10	1.15
51.5	-0.08	1.14
52.0	-0.05	1.11
52.5	-0.03	1.12
53.0	-0.07	1.14
53.5	-0.12	1.11
54.0	-0.13	1.10
54.5	-0.13	1.12
55.0	-0.14	1.12
55.5	-0.12	1.08
56.0	-0.09	1.06
56.5	-0.08	1.06
57.0	-0.09	1.06
57.5	-0.12	1.06
58.0	-0.14	1.06
58.5	-0.18	1.06
59.0	-0.20	1.05
59.5	-0.21	1.06
60.0	-0.24	1.08
60.5	-0.23	1.12
61.0	-0.21	1.14
61.5	-0.21	1.14
62.0	-0.20	1.14
62.5	-0.18	1.15
63.0	-0.18	1.14
63.5	-0.19	1.11
64.0	-0.21	1.11
64.5	-0.21	1.13
65.0	-0.17	1.16
65.5	-0.09	1.16
66.0	-0.06	1.17
66.5	-0.06	1.16
67.0	-0.06	1.16
67.5	-0.08	1.12
68.0	-0.10	1.14
68.5	-0.19	1.14
69.0	-0.22	1.16
69.5	-0.25	1.17
70.0	-0.27	1.19