

Adapter, Coaxial to Waveguide WR19-EFR+

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
40.0	-0.73	-19.27
40.5	-0.67	-19.49
41.0	-0.65	-20.18
41.5	-0.70	-20.36
42.0	-0.69	-19.41
42.5	-0.66	-18.14
43.0	-0.72	-17.47
43.5	-0.73	-17.31
44.0	-0.67	-17.78
44.5	-0.71	-19.39
45.0	-0.72	-21.48
45.5	-0.68	-22.42
46.0	-0.71	-22.96
46.5	-0.71	-25.19
47.0	-0.69	-31.81
47.5	-0.70	-38.96
48.0	-0.69	-26.33
48.5	-0.70	-22.46
49.0	-0.71	-21.04
49.5	-0.71	-20.36
50.0	-0.75	-19.81
50.5	-0.74	-19.72
51.0	-0.72	-19.81
51.5	-0.76	-19.14
52.0	-0.76	-19.18
52.5	-0.74	-20.41
53.0	-0.75	-23.10
53.5	-0.75	-26.50
54.0	-0.75	-27.27
54.5	-0.76	-24.81
55.0	-0.77	-22.94
55.5	-0.79	-21.03
56.0	-0.78	-20.92
56.5	-0.79	-19.73
57.0	-0.82	-18.54
57.5	-0.82	-19.20
58.0	-0.82	-21.84
58.5	-0.84	-28.42
59.0	-0.84	-35.90
59.5	-0.84	-33.23
60.0	-0.88	-31.93