

**Fixed Attenuator****WR22-ATT-20+***Typical Performance Data (+25°C)*

FREQ.	ATTENUATION	WR22 INPUT VSWR	WR22 OUTPUT VSWR
(GHz)	(dB)	(:1)	(:1)
33.0	19.79	1.15	1.08
33.5	19.81	1.15	1.08
34.0	19.77	1.14	1.10
34.5	19.79	1.11	1.09
35.0	19.77	1.09	1.07
35.5	19.79	1.09	1.06
36.0	19.85	1.09	1.05
36.5	19.92	1.07	1.06
37.0	19.96	1.06	1.06
37.5	20.00	1.07	1.05
38.0	20.10	1.08	1.05
38.5	20.20	1.07	1.05
39.0	20.26	1.06	1.04
39.5	20.35	1.06	1.05
40.0	20.48	1.06	1.06
40.5	20.65	1.07	1.07
41.0	20.75	1.06	1.07
41.5	20.80	1.08	1.07
42.0	20.91	1.09	1.05
42.5	21.10	1.08	1.07
43.0	21.33	1.09	1.07
43.5	21.41	1.10	1.07
44.0	21.44	1.11	1.06
44.5	21.59	1.11	1.05
45.0	21.76	1.08	1.04
45.5	21.96	1.09	1.05
46.0	22.07	1.09	1.07
46.5	22.12	1.10	1.05
47.0	22.32	1.13	1.04
47.5	22.56	1.14	1.08
48.0	22.74	1.12	1.09
48.5	22.82	1.10	1.07
49.0	23.01	1.12	1.06
49.5	23.30	1.14	1.05
50.0	23.57	1.14	1.08