

Fixed Attenuator**WR22-ATT-3+***Typical Performance Data (+25°C)*

FREQ.	ATTENUATION	WR22 INPUT VSWR	WR22 OUTPUT VSWR
(GHz)	(dB)	(:1)	(:1)
33.0	2.90	1.06	1.04
33.5	2.91	1.08	1.08
34.0	2.91	1.04	1.05
34.5	2.90	1.07	1.05
35.0	2.93	1.04	1.04
35.5	2.92	1.04	1.06
36.0	2.93	1.05	1.05
36.5	2.96	1.06	1.05
37.0	2.94	1.04	1.04
37.5	2.95	1.05	1.04
38.0	2.99	1.05	1.05
38.5	2.99	1.03	1.05
39.0	2.97	1.04	1.04
39.5	3.00	1.03	1.04
40.0	3.05	1.05	1.04
40.5	3.09	1.05	1.03
41.0	3.07	1.05	1.04
41.5	3.07	1.05	1.04
42.0	3.12	1.04	1.05
42.5	3.15	1.05	1.04
43.0	3.16	1.06	1.04
43.5	3.16	1.04	1.03
44.0	3.18	1.03	1.03
44.5	3.24	1.06	1.04
45.0	3.28	1.04	1.04
45.5	3.27	1.06	1.05
46.0	3.26	1.05	1.04
46.5	3.30	1.03	1.04
47.0	3.36	1.06	1.06
47.5	3.42	1.03	1.04
48.0	3.46	1.06	1.07
48.5	3.45	1.04	1.06
49.0	3.47	1.07	1.05
49.5	3.51	1.07	1.06
50.0	3.58	1.05	1.06

