

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
22.0	76.05	0.23
22.5	74.29	0.20
23.0	84.51	0.15
23.5	86.92	0.05
24.0	88.03	0.01
24.5	81.64	0.04
25.0	85.92	0.05
25.5	77.72	0.05
26.0	83.80	0.05
26.5	88.75	0.06
27.0	72.29	0.06
27.5	77.08	0.06
28.0	82.17	0.02
28.5	74.29	0.00
29.0	72.84	0.01
29.5	89.16	0.01
30.0	74.84	0.06
30.5	73.63	0.07
31.0	74.85	0.03
31.5	72.36	0.03
32.0	80.60	0.05
32.5	71.75	0.02
33.0	80.97	0.01
33.5	78.87	0.05
34.0	77.14	0.18
34.5	71.80	0.27
35.0	74.48	0.22
35.5	71.70	0.13
36.0	50.34	0.10
36.5	20.79	0.53
37.0	0.85	34.63
37.2	0.72	25.22
37.4	0.63	23.94
37.6	0.62	19.63
37.8	0.54	30.32
38.0	0.54	21.31
38.2	0.57	17.66
38.4	0.51	21.48
38.6	0.48	29.84
38.8	0.51	19.76
39.0	0.51	19.06
39.2	0.47	26.75
39.4	0.48	23.64
39.6	0.52	19.43
39.8	0.50	25.14
40.0	0.54	32.09
40.5	7.62	1.43
41.0	24.44	0.18
41.5	35.41	0.21
42.0	44.08	1.05