

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
50.0	104.67	0.01
50.5	106.34	0.01
51.0	105.82	0.01
51.5	103.43	0.05
52.0	104.32	0.04
52.5	102.58	0.02
53.0	117.99	0.06
53.5	100.97	0.01
54.0	120.26	0.05
54.5	111.82	0.02
55.0	101.95	0.01
55.5	80.63	0.05
56.0	54.94	0.11
56.5	16.60	0.87
57.0	0.96	15.14
57.5	0.61	33.46
58.0	0.54	25.05
58.5	0.49	21.20
59.0	0.36	21.51
59.5	0.37	25.39
60.0	0.44	18.34
60.5	0.31	25.74
61.0	0.34	24.16
61.5	0.28	27.24
62.0	0.34	17.38
62.5	0.24	36.07
63.0	0.30	20.85
63.5	0.29	34.86
64.0	0.27	21.55
64.5	0.30	22.29
65.0	0.33	19.90
65.5	0.36	21.92
66.0	0.52	24.07
66.5	16.32	0.36
67.0	35.88	0.12
67.5	49.54	0.07
68.0	60.22	0.05
68.5	68.84	0.01
69.0	75.99	0.00
69.5	83.05	0.00
70.0	88.17	0.02
70.5	95.08	0.03
71.0	95.37	0.03
71.5	101.49	0.01
72.0	102.09	0.09
72.5	94.92	0.02
73.0	102.40	0.02
73.5	96.47	0.00
74.0	102.13	0.01
75.0	98.84	0.01