

Typical Performance Data

FREQUENCY	INSERTION LOSS	RETURN LOSS
(GHz)	(dB)	(dB)
50.0	62.55	0.01
51.0	84.01	0.04
52.0	77.80	0.00
53.0	75.20	0.06
54.0	79.63	0.00
55.0	80.92	0.03
56.0	87.87	0.09
57.0	88.17	0.05
58.0	80.55	0.06
59.0	87.88	0.09
60.0	68.35	0.14
60.5	46.68	0.21
61.0	12.35	1.60
61.5	1.13	23.50
61.8	0.96	26.65
62.0	0.88	22.10
62.3	0.81	24.62
62.5	0.80	21.16
62.8	0.75	31.81
63.0	0.76	24.42
63.3	0.79	24.43
63.5	0.86	23.56
63.8	1.04	20.15
64.0	5.15	3.61
64.3	20.20	0.44
64.5	32.02	0.20
64.8	41.24	0.11
65.0	48.82	0.11
65.3	55.32	0.09
65.5	60.89	0.06
65.8	65.41	0.01
66.0	70.66	0.03
66.3	73.22	0.03
66.5	75.38	0.02
66.8	79.65	0.02
67.0	84.29	0.01
67.3	84.18	0.07
67.5	86.46	0.07
67.8	80.62	0.02
68.0	81.16	0.04
68.3	86.32	0.00
68.5	86.74	0.06
68.8	88.31	0.06
69.0	86.08	0.05
70.0	90.77	0.05
71.0	82.50	0.04
72.0	91.54	0.00
73.0	84.28	0.04
74.0	78.54	0.04
75.0	81.17	0.10