

Typical Performance Data

FREQUENCY	INSERTION LOSS	RETURN LOSS
(GHz)	(dB)	(dB)
50.0	92.25	0.05
51.0	94.87	0.03
52.0	98.94	0.03
53.0	101.59	0.04
54.0	104.70	0.05
55.0	102.57	0.04
56.0	97.50	0.03
57.0	106.37	0.00
58.0	110.18	0.01
59.0	103.66	0.02
60.0	100.80	0.08
60.5	97.76	0.07
61.0	92.19	0.11
61.5	78.32	0.12
61.8	70.54	0.15
62.0	61.91	0.15
62.3	51.87	0.19
62.5	40.01	0.29
62.8	24.95	0.55
63.0	5.47	4.58
63.3	1.35	22.03
63.5	1.13	16.83
63.8	0.87	28.67
64.0	0.81	26.11
64.3	0.75	23.39
64.5	0.73	21.03
64.8	0.68	30.63
65.0	0.72	18.41
65.3	0.69	21.47
65.5	0.73	26.51
65.8	0.76	30.88
66.0	1.05	18.68
66.3	4.80	3.72
66.5	18.19	0.51
66.8	29.12	0.22
67.0	37.85	0.16
67.3	44.75	0.08
67.5	50.83	0.09
67.8	56.15	0.09
68.0	60.65	0.07
68.3	64.82	0.06
68.5	68.40	0.04
68.8	71.44	0.02
69.0	74.61	0.05
70.0	83.69	0.04
71.0	90.11	0.04
72.0	94.41	0.05
73.0	94.55	0.02
74.0	98.75	0.05
75.0	102.42	0.02