

*Typical Performance Data*

FREQUENCY (GHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
60.0	66.67	0.31
60.5	60.16	0.24
61.0	53.21	0.28
61.5	45.24	0.27
62.0	36.52	0.35
62.5	26.04	0.24
63.0	13.02	0.75
63.5	1.11	10.82
64.0	0.50	22.45
64.5	0.48	22.11
65.0	0.39	22.89
65.5	0.49	29.07
66.0	0.26	20.05
66.5	0.31	23.91
67.0	0.33	28.71
67.5	0.30	20.01
68.0	0.35	21.45
68.5	0.17	41.71
69.0	0.41	21.46
69.5	0.34	18.15
70.0	0.15	23.41
70.5	0.37	28.27
71.0	0.21	23.52
71.5	0.55	13.78
72.0	3.94	2.62
72.5	10.38	0.35
73.0	16.60	0.25
73.5	21.85	0.32
74.0	25.93	0.13
74.5	29.64	0.13
75.0	32.66	0.10
75.5	35.37	0.21
76.0	37.83	0.09
76.5	39.73	0.33
77.0	41.32	0.19
77.5	42.94	0.26
78.0	44.30	0.37
78.5	45.18	0.10
79.0	46.59	0.22
80.0	47.73	0.17
81.0	48.71	0.09
82.0	48.68	0.18
83.0	48.75	0.28
84.0	48.09	0.26
85.0	46.66	0.16
86.0	45.06	0.19
87.0	42.69	0.08
88.0	40.51	0.21
89.0	37.30	0.48
90.0	32.92	0.60