

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING		RETURN LOSS		
		(dB)		(dB)		
		IN-CPL	OUT-CPL	IN	OUT	CPL
100	0.05	26.50	26.47	34.80	35.47	14.51
120	0.06	26.42	26.37	33.53	33.98	16.64
140	0.06	26.36	26.30	31.64	32.45	18.66
160	0.07	26.30	26.22	30.06	31.18	20.58
180	0.08	26.25	26.14	29.62	30.33	22.43
200	0.08	26.21	26.07	28.80	29.55	24.20
220	0.09	26.16	26.01	27.89	28.80	25.65
240	0.10	26.11	25.92	27.25	28.02	26.41
260	0.10	26.06	25.84	26.63	27.27	26.30
280	0.11	26.00	25.75	25.99	26.74	25.61
300	0.11	25.94	25.66	25.41	26.27	24.68
320	0.12	25.88	25.56	24.94	25.87	23.63
340	0.12	25.81	25.45	24.52	25.49	22.54
360	0.13	25.73	25.35	24.18	25.21	21.47
380	0.13	25.65	25.23	23.89	24.94	20.50
400	0.14	25.56	25.11	23.63	24.72	19.64
420	0.14	25.46	24.98	23.41	24.50	18.89
440	0.15	25.35	24.84	23.20	24.38	18.20
460	0.15	25.23	24.70	23.08	24.32	17.55
480	0.16	25.10	24.55	22.96	24.25	16.91
500	0.16	24.96	24.38	22.91	24.21	16.31
512	0.16	24.86	24.28	22.87	24.21	15.98
520	0.16	24.80	24.20	22.85	24.24	15.76
530	0.17	24.71	24.11	22.84	24.27	15.50
540	0.17	24.62	24.01	22.86	24.31	15.24
550	0.17	24.53	23.90	22.86	24.37	14.98