

16 Way-0° Power Splitter/Combiner

ZC16PD-960+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB) S-1	AMP. UNBAL. (dB)	ISOLATION (dB)		FREQ. (MHz)	VSWR (:1)	
			1-2	1-9		S	1
890.0	12.37	0.24	30.43	41.59	890.0	1.09	1.00
898.0	12.39	0.24	30.07	40.94	898.0	1.07	1.01
901.8	12.30	0.22	29.88	40.62	901.8	1.07	1.01
907.8	12.38	0.25	29.58	40.17	907.8	1.06	1.01
915.3	12.39	0.23	29.16	39.64	915.3	1.04	1.01
919.8	12.37	0.25	28.89	39.39	919.8	1.04	1.02
925.0	12.39	0.24	28.61	39.06	925.0	1.04	1.02
930.3	12.38	0.25	28.30	38.77	930.3	1.03	1.02
938.5	12.39	0.26	27.83	38.25	938.5	1.03	1.03
942.3	12.37	0.24	27.60	38.08	942.3	1.04	1.03
946.8	12.39	0.25	27.29	37.83	946.8	1.04	1.03
953.5	12.36	0.26	26.89	37.51	953.5	1.06	1.03
957.3	12.38	0.24	26.68	37.30	957.3	1.06	1.04
958.0	12.37	0.26	26.63	37.28	958.0	1.07	1.04
960.0	12.39	0.25	26.51	37.19	960.0	1.07	1.04

¹ Total Loss = Insertion Loss+ 12dB Splitter Loss

REV. X2
ZZC16PD-960+
100627
Page 1 of 1