

Typical Performance Data

CARRIER FREQ.	CONVERSION LOSS	SIDE BAND REJECTION		CARRIER REJECTION		3rd HARMONIC SUPPRESSION		5th HARMONIC SUPPRESSION		DC OFFSET
		LSB	USB	LSB	USB	LSB	USB	LSB	USB	
(MHz)	(dB)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(mV)
86.00	5.43	38.25	38.49	47.39	47.41	47.59	53.41	75.27	77.69	0.37
86.70	5.44	38.88	38.76	47.31	47.24	47.45	53.41	76.83	78.37	0.36
87.40	5.44	39.63	39.13	47.26	46.98	47.43	53.21	78.67	79.85	0.36
87.70	5.44	39.92	39.24	47.12	47.06	47.47	53.28	78.61	80.58	0.36
88.10	5.44	40.07	39.46	47.09	47.03	47.47	53.36	79.35	80.87	0.36
88.80	5.45	40.65	40.03	47.07	47.04	47.61	53.31	81.11	82.87	0.37
89.30	5.45	40.92	40.31	46.95	46.77	47.57	53.45	82.03	82.83	0.37
89.60	5.45	41.33	40.49	46.93	46.95	47.69	53.41	82.17	83.19	0.36
90.30	5.45	41.81	40.74	46.86	46.89	47.83	53.73	82.93	83.93	0.36
91.00	5.45	41.90	41.32	46.84	46.76	47.93	53.87	81.69	82.39	0.36
91.00	5.45	42.04	41.44	46.86	46.74	47.95	53.85	81.69	83.45	0.36
91.40	5.46	42.53	41.58	46.81	46.63	47.98	54.05	81.60	81.45	0.37
92.20	5.45	42.75	42.00	46.56	46.52	48.17	54.33	82.23	81.55	0.37
92.60	5.46	42.71	42.24	46.64	46.45	48.33	54.37	80.81	80.47	0.37
92.90	5.45	42.83	42.24	46.53	46.54	48.29	54.49	81.21	80.15	0.36
93.60	5.46	43.10	43.00	46.43	46.24	48.58	54.97	79.58	78.29	0.36
94.30	5.46	42.97	43.22	46.26	46.25	48.76	55.09	78.26	78.29	0.37
94.50	5.46	42.97	43.37	46.21	46.10	48.77	55.14	78.45	77.70	0.37
94.80	5.46	42.93	43.40	46.27	46.13	48.91	55.36	78.95	77.40	0.37
95.00	5.46	42.82	43.50	46.23	46.17	48.89	55.30	78.71	76.78	0.38