

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10	0.02	55.08	6000	0.38
100	0.05	38.29	6125	0.39
500	0.15	23.00	6250	0.39
1000	0.26	17.57	6375	0.39
4500	1.50	8.78	6500	0.40
5000	1.40	9.81	6625	0.40
6000	0.78	18.91	6750	0.40
7500	1.13	13.13	6875	0.40
9000	2.12	12.97	7000	0.40
9500	3.25	13.68	7125	0.39
9750	7.35	4.72	7250	0.39
10000	15.18	2.76	7375	0.40
10150	20.68	2.59	7500	0.42
10400	31.91	2.65	7625	0.42
10800	29.61	2.96	7750	0.43
11500	23.55	3.87	7875	0.44
12000	21.23	4.53	8000	0.44
13000	22.17	4.08	8125	0.45
13500	30.90	2.52	8250	0.46
14000	32.38	1.10	8375	0.47
14500	43.35	0.84	8500	0.48
15000	41.68	2.20	8625	0.49
16000	28.90	8.69	8750	0.50
17000	21.81	2.40	9000	0.55