

3 Way-0° Power Splitter/Combiner

ZN3PD-900

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	ISOLATION (dB)		FREQ. (MHz)	VSWR (:1)			
	S-1	S-2	S-3		1-2	2-3		S	1	2	3
800	4.97	4.89	4.96	0.08	29.34	29.71	800	1.11	1.05	1.05	1.06
807	4.99	4.90	4.96	0.10	30.20	30.67	807	1.09	1.05	1.05	1.06
815	4.97	4.91	4.94	0.07	31.25	31.77	815	1.08	1.06	1.05	1.06
824	4.97	4.92	4.94	0.05	32.52	33.23	824	1.06	1.06	1.05	1.06
827	4.97	4.92	4.94	0.05	32.95	33.71	827	1.05	1.06	1.05	1.06
832	4.97	4.93	4.93	0.05	33.62	34.51	832	1.04	1.06	1.05	1.07
842	4.96	4.94	4.94	0.02	34.95	36.11	842	1.02	1.06	1.04	1.07
855	4.96	4.96	4.92	0.04	35.80	37.18	855	1.02	1.06	1.04	1.07
865	4.95	4.97	4.92	0.05	35.47	36.69	865	1.04	1.06	1.04	1.07
867	4.96	4.98	4.91	0.06	35.39	36.51	867	1.04	1.06	1.04	1.07
875	4.94	4.99	4.91	0.08	34.47	35.32	875	1.06	1.06	1.04	1.07
882	4.97	5.01	4.92	0.08	33.54	34.24	882	1.08	1.06	1.04	1.07
890	4.95	5.02	4.93	0.09	32.42	32.96	890	1.09	1.06	1.04	1.07
896	4.94	5.03	4.90	0.13	31.57	32.01	896	1.11	1.06	1.05	1.07
900	4.97	5.04	4.92	0.12	31.01	31.40	900	1.12	1.06	1.05	1.07

¹ Total Loss = Insertion Loss+ 4.8dB Splitter Loss

REV. X2
ZN3PD-900
100627
Page 1 of 1