

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
100	82.90	0.03	11200	9.04
500	98.83	0.04	11205	8.44
1000	94.28	0.09	11210	7.98
10940	70.17	0.20	11215	7.64
11000	59.77	0.25	11220	7.37
11150	15.45	1.42	11230	6.93
11120	28.59	0.64	11240	6.58
11150	15.45	1.42	11250	6.33
11175	3.79	9.88	11260	6.18
11200	2.00	18.39	11270	6.07
11250	1.60	18.56	11280	5.98
11300	1.55	17.56	11290	5.90
11350	1.67	18.93	11300	5.84
11400	2.03	18.93	11310	5.83
11425	2.95	17.10	11320	5.86
11450	11.04	2.24	11330	5.93
11490	28.55	0.58	11340	5.99
11550	45.96	0.32	11350	6.07
11600	56.52	0.26	11360	6.20
11680	69.48	0.22	11370	6.43
12000	95.78	0.19	11380	6.75
15000	104.06	0.39	11390	7.15
17000	103.53	0.27	11395	7.38
20000	99.79	0.21	11400	7.64