

Band Pass Filter

CBPF-EDU0560

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.00	82.12	0.00	1.00	62.61
20.00	86.20	0.02	10.00	27.19
50.00	90.87	0.05	40.00	0.38
60.00	90.47	0.06	60.00	5.23
70.00	86.83	0.08	92.00	21.74
92.00	68.64	0.14	107.00	37.81
105.00	46.63	0.37	116.00	38.31
107.00	41.01	0.51	117.00	38.25
111.50	24.77	1.56	118.00	38.19
112.00	22.69	1.74	119.00	38.14
115.00	10.87	13.68	120.00	38.08
119.00	4.30	17.17	121.00	38.23
122.00	4.10	16.24	122.00	38.46
125.00	5.48	16.16	123.00	38.69
128.00	10.22	10.05	124.00	38.92
130.70	25.51	3.41	125.00	38.84
134.00	40.88	0.87	126.00	38.75
135.00	45.19	0.67	127.00	38.65
140.00	60.99	0.38	128.00	38.53
152.00	81.54	0.21	135.00	37.40
225.00	78.63	0.14	152.00	25.58
375.00	72.46	0.18	175.00	2.40
800.00	69.07	0.25	250.00	0.65
1600.00	61.08	0.30	400.00	0.62
2400.00	58.39	0.39	500.00	0.15
3200.00	37.93	8.22	1000.00	0.37
3800.00	26.36	2.06	2000.00	0.61
4600.00	23.69	2.62	4000.00	2.91
5200.00	33.05	2.28	5000.00	2.45
6000.00	34.06	4.03	6000.00	2.62