



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.002

| CASE # | A | B | C | D | E | F | G | H | J | K |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|----------------|----------------|
| DG1886 | .157 (4.00) | .157 (4.00) | .035 (0.90) | .009 (0.24) | .098 (2.50) | .098 (2.50) | .012 (0.30) | -- -- | .018 (0.45) | .026 (0.65) |

| CASE # | L | M | N | P | Q | R | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|---------------|----------|
| DG1886 | .185 (4.70) | .185 (4.70) | .085 (2.16) | .014 (0.36) | .035 (0.89) | .85 (2.16) | .04 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.