



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K
DG983-3	.157 (4.00)	.157 (4.00)	.037 (0.94)	.028 (0.70)	.079 (2.00)	.079 (2.00)	.010 (0.26)	.004 (0.10)	.016 (0.40)	.020 (0.50)

CASE #	L	M	N	P	Q	R	WT. GRAM
DG983-3	.165 (4.20)	.165 (4.20)	.081 (2.05)	.012 (0.31)	.024 (0.60)	.081 (2.05)	.04

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: 0.2 μ inches of Gold (Au) over 0.1 μ inches of Palladium (Pd) over 10 μ inches of Nickel (Ni). All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

