



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K
DG984-1	.157 (4.00)	.157 (4.00)	.029 (0.75)	.008 (0.20)	.106 (2.70)	.106 (2.70)	.010 (0.25)	.002 (0.05)	.016 (0.40)	.020 (0.50)

CASE #	L	M	N	P	Q	R	WT. GRAM
DG984-1	.173 (4.40)	.173 (4.40)	.108 (2.75)	.012 (0.30)	.024 (0.60)	.108 (2.75)	.04

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: NiPdAu. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.